

REFLEX ANTI-HOLOGRAMM



Finish polish



Rotary
800-1200 rpm



Forced orbital
5400-9000 rpm



Random orbital
300-600 rpm



Pads



1L



250 ml

Art-Nr. 15800001 • 1 Liter • VPE 8 Stück
Art-Nr. 15800250 • 250 ml • VPE 12 Stück



Cut 2

Brilliant features

- ✓ Silicone-free
- ✓ for fresh and weathered paints
- ✓ without sealing components
- ✓ wet look finish
- ✓ For fresh and weathered paints

Product Description

Reflex Anti-Hologram is a finish polish designed to remove holograms, gray haze, fine swirl marks, and paint defects. It is particularly easy to apply. The containing ultrafine grinding components leave a brilliant deep shine on fresh and weathered paints.

Pad Recommendation:

- Anti-Hologram Pad, purple – suitable for all paint finishes
- Finish Pad, green – suitable for all paint finishes



Anwendung

Step 1

Preparation

Prepare the surface using an abrasive rubber/Prepa-Pad and a lubricator to remove coarse and fine deposits. Depending on the condition of the paint, we recommend using the Diamant Series rubbing compounds during the initial polishing steps to achieve an optimal paint finish. To visually assess the polishing result, we recommend using our Wipe Down Spray.

Step 2

Application & Processing

Apply Reflex Anti-Hologram evenly to the purple POLYTOP Anti-Hologram Pad or the green Finish Pad, work it into the paint surface in sections, and polish in a crisscross pattern. For free-running orbital polishers, we recommend a medium to high speed without pressure. For rotary or forced-orbital machines, use a low to medium speed with light pressure. Blow the polishing sponge clean with compressed air after each panel to ensure consistent performance and maximum results.

Step 3

Inspection & Touch-ups

To check the results, remove any polish residue and degrease the paint surface using Wipe Down Spray and a scratch-free microfiber cloth. To do this, spray each component with the degreaser and let it sit for 30–60 seconds.

Tips and tricks

- For delicate solid-color paints and extremely soft paints, we recommend the POLYTOP Finish Pad (green).
 - By applying two to three drops of Polishing Assistant to the blown-out cutting pad and the remaining polish residue, an additional high gloss can be achieved at low to medium speeds.
- Power Nap:** To preserve the pad, we recommend allowing the polishing sponge a regeneration break after each component before reusing it. In the meantime, you can continue working with a second pad.

With the 2026 formula update, Reflex Anti-Hologram has been given significantly more cutting power and an improved finish – regardless of whether it is applied using a rotary or orbital polisher. This allows all Diamant rubbing compounds to be used in a two-step system:

1. Polishing step: Select a rubbing compound from the Diamant series and apply it with a foam pad or microfiber pad.
2. Polishing step: Reflex Anti-Hologram.

Depending on the paint hardness and the remaining surface condition, Reflex Anti-Hologram can be used immediately after cutting work with lambskin pads.

Complementary products

- WIPE DOWN SPRAY
- ANTI-HOLOGRAM PAD PURPLE
- FINISH PAD GREEN
- MICROFIBER CLOTH SOFT EDGELESS REFLEX VIOLET



Further product recommendation

- Diamant 2000
- Diamant 3000
- Diamant 5000
- Diamant 7000



You can find these and other products under: <https://online.flippingbook.com/view/77451888/>

Applications

- Paint and fiberglass on passenger cars, commercial vehicles, motorcycles, trailers, motorhomes, boats, etc.
- Powder-coated surfaces with clear coat
- High-gloss trim in exterior and interior applications

Directions for use

Shake the bottle well before use. Do not use the product in direct sunlight or on hot surfaces.

Application temperature

10°C bis maximal +35°C

Storage and shelf life

At least 24 months when kept in the original, unopened container at room temperature.
Protect the product from direct sunlight and frost! Storage temperature: +4°C to +30°C

POLYTOP GmbH
Schafweide 2
63762 Großostheim
Deutschland

Telefon: +49 6026 99577-0
E-Mail: info@polytop.de